

Generator set data sheet

1200 kW continuous



Model: C1200 N5C
Frequency: 50 Hz
Fuel type: Natural gas MI 62 +
Emissions performance NOx: 250 Mg/Nm³
LT water inlet temperature: 40 °C (104 °F)
HT water outlet temperature: 90 °C (194 °F)

Measured sound performance data sheet:	N/A
Prototype test summary data:	N/A
Remote radiator cooling outline:	A029U550 normal duty air filtration A029E093 heavy duty air filtration

Fuel consumption (ISO3046/1)	See note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
Fuel consumption (LHV) ISO3046/1, kW (MMBTU/hr)	2,3,6,11	2947 (10.06)	2675 (9.14)	2313 (7.9)	-
Mechanical efficiency ISO3046/1, percent	2,3,6	41.9%	41.6%	40.2%	-
Electrical efficiency ISO3046/1, percent	2,3,6,11	40.7%	40.4%	38.9%	-

Engine

Engine manufacturer	Cummins
Engine model	QSK60G
Configuration	V16
Displacement, L (cu.in.)	60 (3671)
Aspiration	Turbocharged (1)
Gross engine power output, kWm (hp)	1236 (1657)
BMEP, bar (psi)	16.5 (239.25)
Bore, mm (in.)	159 (6.26)
Stroke, mm (in.)	190 (7.48)
Rated speed, rpm	1500
Piston speed, m/s (ft/min)	9.5 (1870)
Compression ratio	13.7:1
Lube oil capacity, L (qt)	380 (400)
Overspeed limit, rpm	1875
Full load lubricating oil consumption, g/kWe-hr (g/hp-hr)	0.15 (0.11)

Fuel

Gas supply pressure to engine inlet, bar (psi) ⁶	0.20 (2.9)
Minimum methane index	62

Starting system(s)

Electric starter voltage, volts	24
Minimum battery capacity @ 40 °C (104 °F), AH	450
Air starter pressure, barg (psig)	N/A
Air starter flow Nm ³ /s (scfm)	N/A

Genset dimensions (see note 1)

Genset length, m (ft)	5.12 (16.8)
Genset width, m (ft)	2.23 (7.30)
Genset height, m (ft)	2.77 (9.08)
Genset weight (wet), kg (lbs)	15450 (33,990)

	See note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
Energy data					
Continuous generator electrical output kWe @ 1.0 pf	9,11	1200	1080	900	-
Total heat rejected in LT circuit, kW (MMBTU/h)	4	98 (0.34)	86 (0.30)	70 (0.24)	-
Total heat rejected in HT circuit, kW (MMBTU/h)	4	605 (2.06)	543 (1.85)	495 (1.69)	-
Unburnt, kW (MMBTU/h)	12	92 (0.32)	84 (0.29)	61 (0.21)	-
Heat radiated to ambient, kW (MMBTU/h)	12	189 (0.64)	172 (0.59)	149 (0.51)	-
Available exhaust heat to 105 °C, kW (MMBTU/h)	4	737 (2.51)	686 (2.34)	561 (1.91)	-
Intake air flow					
Intake air flow mass, kg/s (lb/hr)	3	1.82 (14410)	1.65 (13070)	1.26 (9980)	-
Intake air flow volume, m ³ /s @ 0 °C (scfm)	3	1.41 (3150)	1.28 (2860)	0.97 (2170)	-
Max air cleaner restriction below 35 °C, mm HG (in H ₂ O)		28 (15.0)	-	-	-
Max air cleaner restriction above 35 °C, mm HG (in H ₂ O)		14 (7.3)	-	-	-
Exhaust air flow					
Exhaust gas flow mass, kg/s (lb/hr)	3	1.88 (14890)	1.71 (13540)	1.30 (10300)	-
Exhaust gas flow volume, m ³ /s (cfm)	3	3.85 (8150)	3.55 (7520)	2.80 (5930)	-
Exhaust temp after turbine, °C (°F)	2,11	450 (841)	459 (858)	486 (907)	-
Max exhaust system back pressure, mm HG (in H ₂ O)	11,13	28.0 (15.0)	-	-	-
Min exhaust system back pressure, mm HG (in H ₂ O)	11,13	-	-	-	-
HT cooling circuit					
HT circuit engine coolant volume, l (gal)		181 (48)	181 (48)	181 (48)	-
HT coolant flow @ max ext restriction, m ³ /h (gal/min)		70 (310)	70 (310)	70 (310)	-
Max HT engine coolant inlet temp, °C (°F)	7	80 (176)	80 (177)	82 (180)	-
HT coolant outlet temp, °C (°F)	7	90 (194)	90 (194)	90 (194)	-
Max pressure drop in external HT circuit, bar (psig)		1.0 (15)	1.0 (15)	1.0 (15)	-
HT circuit max pressure, bar (psig)		5.0 (73)	5.0 (73)	5.0 (73)	-
Min static head - pump inlet, bar (psig)		0.5 (7)	0.5 (7)	0.5 (7)	-
LT cooling circuit					
LT circuit engine coolant volume, l (gal)		34 (9)	34 (9)	34 (9)	-
LT coolant flow @ max ext restriction, m ³ /h (gal/min)		23 (101)	23 (101)	23 (101)	-
Max LT engine coolant inlet temp, °C (°F)	8	40 (104)	40 (104)	40 (104)	-
LT coolant outlet temp, °C (°F) reference only	8	50 (122)	50 (122)	50 (122)	-
Max pressure drop in external LT circuit, bar (psig)		1.0 (15)	1.0 (15)	1.0 (15)	-
LT circuit max pressure, bar (psig)		5.0 (73)	5.0 (73)	5.0 (73)	-
Min static head - pump inlet, bar (psig)		0.5 (7)	0.5 (7)	0.5 (7)	-

	See note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
Emissions					
NO _x emissions dry, ppm	14	87	86	92	-
NO _x emissions, mg/Nm ³ @ 5% O ₂ (g/hp-h)	14	200 (0.50)	200 (0.50)	200 (0.50)	-
THC emissions wet, ppm	12	1696	1707	1612	-
THC emissions, mg/Nm ³ @ 5% O ₂ (g/hp-h)	12	1878 (4.00)	1876 (4.00)	1714 (4.00)	-
NMHC emissions wet, ppm	12	339	341	322	-
NMHC exhaust emissions, mg/Nm ³ (g/hp-h)	12	380 (0.8)	380 (0.8)	380 (0.8)	-
CO emissions (dry), ppm	12	529	508	469	-
CO emissions, mg/Nm ³ @ 5% O ₂ (g/hp-h)	12	910 (1.90)	860 (1.80)	770 (1.70)	-
CO ₂ emissions (dry), percent	12	6.5	6.6	6.8	-
O ₂ emissions (dry), percent	12	9.3	9.2	8.8	-
Particulates PM10, g/hp-h	12	< 0.03	< 0.03	< 0.03	-

Genset de-rating

Altitude and temperature derate multiplication factor

Barometer		Altitude		Table A * Derate multiplier with grid parallel operation								
In Hg	mbar	Feet	Meters									
20.7	701	9843	3000	0.88	0.88	0.82	0.79	0.71	0.62	-	-	-
21.4	723	9022	2750	0.92	0.91	0.85	0.82	0.73	0.63	-	-	-
22.1	747	8202	2500	0.96	0.95	0.89	0.84	0.75	0.64	-	-	-
22.8	771	7382	2250	1.00	0.98	0.93	0.87	0.76	0.64	-	-	-
23.5	795	6562	2000	1.00	1.00	0.97	0.90	0.78	0.65	-	-	-
24.3	820	5741	1750	1.00	1.00	1.00	0.95	0.79	0.66	-	-	-
25.0	846	4921	1500	1.00	1.00	1.00	0.99	0.81	0.66	-	-	-
25.8	872	4101	1250	1.00	1.00	1.00	1.00	0.83	0.67	-	-	-
26.6	899	3281	1000	1.00	1.00	1.00	1.00	0.84	0.68	-	-	-
27.4	926	2461	750	1.00	1.00	1.00	1.00	0.86	0.68	-	-	-
28.3	954	1640	500	1.00	1.00	1.00	1.00	0.88	0.69	-	-	-
29.1	983	820	250	1.00	1.00	1.00	1.00	0.88	0.69	-	-	-
29.5	995	492	150	1.00	1.00	1.00	1.00	0.88	0.69	-	-	-
30.0	1012	0	0	1.00	1.00	1.00	1.00	0.88	0.69	-	-	-
			°C	20	25	30	35	40	45	50	55	60
			°F	68	77	86	95	104	113	122	131	140
			Air filter inlet temperature									

* Based on SAE standard ambient pressure vs. altitude. Assumes LT return temperature is 10 °C above air filter inlet.

Temperature & altitude derate

1. Determine derate multiplier vs. temperature and altitude in Table A depending upon your operating condition.
2. Assumes the LT return temperature is 10°C above the air filter inlet with a maximum LT temperature of 50°C.
3. If the LT temperature exceeds 50°C, consult factory for recommendations.
4. Altitude is based upon SAE standard ambient pressure vs. altitude. For low barometric conditions add 150 m (500 ft) to site altitude.

Heat rejection factor (altitude and ambient) for HT and LT circuits

Barometer		Altitude		Table B Multiplier for HT & LT heat rejection vs alt & temp.								
In Hg	mbar	Feet	Meters									
20.7	701	9843	3000	1.06	1.10	1.11	1.13	1.14	1.15	1.17	1.18	1.19
21.4	723	9022	2750	1.05	1.09	1.10	1.12	1.13	1.14	1.15	1.17	1.18
22.1	747	8202	2500	1.04	1.08	1.09	1.10	1.12	1.13	1.14	1.16	1.17
22.8	771	7382	2250	1.03	1.07	1.08	1.09	1.11	1.12	1.13	1.14	1.16
23.5	795	6562	2000	1.02	1.06	1.07	1.08	1.09	1.11	1.12	1.13	1.15
24.3	820	5741	1750	1.01	1.04	1.06	1.07	1.08	1.10	1.11	1.12	1.14
25.0	846	4921	1500	0.99	1.03	1.05	1.06	1.07	1.09	1.10	1.11	1.12
25.8	872	4101	1250	0.98	1.02	1.04	1.05	1.06	1.07	1.09	1.10	1.11
26.6	899	3281	1000	0.97	1.01	1.02	1.04	1.05	1.06	1.08	1.09	1.10
27.4	926	2461	750	0.96	1.00	1.01	1.03	1.04	1.05	1.07	1.08	1.09
28.3	954	1640	500	0.95	0.99	1.00	1.02	1.03	1.04	1.05	1.07	1.08
29.1	983	820	250	0.94	0.98	0.99	1.00	1.02	1.03	1.04	1.06	1.07
29.5	995	492	150	0.94	0.97	0.99	1.00	1.01	1.03	1.04	1.05	1.06
30.0	1012	0	0	0.93	0.97	0.98	0.99	1.01	1.02	1.03	1.05	1.06
			°C	20	25	30	35	40	45	50	55	60
			°F	68	77	86	95	104	113	122	131	140
			Air filter inlet temperature									

LT & HT circuit heat rejection calculation

1. Determine derate multiplier vs. temperature derate per Table A.
2. Using the multiplier from #1 in Table A as the percent load factor determine the heat rejection from the previous page.
3. From Table B find the HT and LT circuit multiplier.
4. Multiply the result of step 2 by the result of step 3 to obtain the heat rejection at your altitude and temperature.

Methane number vs LT temp - table C ⁴

Methane number	LT return temperature		
	40 °C	45 °C	50 °C
72	Green	Green	Green
67	Green	Green	Yellow
62	Green	Yellow	Yellow
57	Yellow	Yellow	Red
52	Yellow	Red	Red

Methane number capability

Load (percent of rated)			
100%	90%	75%	50%
62	60	60	-

Alternator data

Voltage range	Connection configuration	Temp rise degrees C	Duty ¹⁰ cycle	Single phase factor	Alternator data sheet	Feature code
380-440	Wye, 3 Phase	80	C	N/A	334	B703-2
3300	Wye, 3 Phase	80	C	N/A	518	B592-2
6300-6600	Wye, 3 Phase	80	C	N/A	521	B593-2
10000	Wye, 3 Phase	80	C	N/A	521	B794-2
10500-11000	Wye, 3 Phase	80	C	N/A	521	B835-2

Continuous rating definition

Applicable for supplying power continuously to a constant load up to the full output rating for unlimited hours. No sustained overload capability is available for this rating. Consult authorized distributor for rating (equivalent to continuous power in accordance with ISO8528, ISO3046, AS2789, DIN6271, and BS5514).

Notes

- 1) Weights and set dimensions represent a generator set with its standard features only. See outline drawing for other configurations.
- 2) At ISO3046 reference conditions, altitude 1013 mbar (30 in. Hg), air inlet temperature 25 °C (77 °F).
- 3) According to ISO3046/I with fuel consumption tolerance of +5% -0%.
- 4) Production variation/tolerance ±10%.
- 5) With air intake at 25 °C (77 °F). Tolerance ± 10 °F.
- 6) Tested using pipeline natural gas with LHV of 33.44 mJ/Nm³ (905 BTU/ft³).
- 7) Outlet temperature controlled by thermostat. Inlet temperature for reference only.
- 8) Inlet temperature controlled by thermostat. Outlet temperature for reference only.
- 9) With off engine coolant pumps.
- 10) Standby (S), Prime (P), Continuous (C).
- 11) At electrical output of 1.0 power factor.
- 12) Tolerance +/- 15%.
- 13) Exhaust system back pressure is at rated load and will decrease at lower loads.
- 14) Tolerance ±10% for 500 mg, ±14% for 350 mg & ±20% for 250 mg.

For more information contact your local Cummins distributor
or visit power.cummins.com

Our energy working for you.™

